Eltech



Sealed for Protection

Sealed for Protection

Sealed for Protection

Sealed for Protection Sealed for Protection

Sealed for Protection

Sealed for Protection




NUCTION CAP SEALER SEMI AUTOMATIC


Introduction

Induction sealing is a non-contact heating process, which is used to bond a foil disk or to seal the opening of a container. The technique provides the user with a tamper evident seal.





Cap foil construction



Operating Principle

The principle of operation lies in the cap, which passes through an electromagnetic field generated by an induction sealing head on a conveyor. The electromagnetic filed induces a high electric current in the foil of seal. This causes the foil in the seal to heat. A coating laminated to the aluminum disk fuses and softens to the mouth of the bottle.

Advantage



- Tamper Evidence Deter Pilferage
- Increased Shelf Life Product Freshness
- Free from oxidation and contamination
- Sealed for consumer confidence
- Leak Prevention no rejection, hence enhanced profits
- A sealed product is perceived to be safe and hygienic

Features Of S-500

- ◆Advanced Mosfet /IGBT technology Delivers high efficiency sealing power and long term reliability.
- Sealing head slide mount provides hands-free sealing head operation and eliminates operator fatigue from holding sealing head.
- It requires no water and is 100 % air cooled.
- ⇒LCD display screen with touch buttons for easy use
- ⇒Digital UP/Down timer: Provides precise timing from 0.1 to 9.9 seconds.
- ⇒Batch count and batch preset
- ⇒Total number of bottles sealed
- Programmed recipes and menus allows quick /easy adjustments between applications
- ⇒Visual and audible alarms
- TV" stop centering guide for assurance of bottle being under sealing head.
- ⇒Foot switch for easy start-up of sealing machine.
- ⇒No tools are required for adjustment or set-up.
- Can seal PET / HDPE / PP / LDPE / PVC / GLASS containers.

S-500

Eltech S-500, Semi-Automatic Induction Cap Sealer is specifically designed for packagers who require a semi-automatic sealing process with low production volumes. The table top model is compact and ideal for production environments where a bottle conveyor is not practical. Built-in guides ensure operators properly line-up containers for sealing. A digital timer lets the operator know when the sealing process is completed. This model is suitable for batch type production and can be used continuously for 24hrs x 365 days Ideal for laboratory use, stability testing, r & d facilities, short runs test marketing.

Ideal For

Laboratory Use, Stability Testing, R & D Facilities, Short Runs Test Marketing, A Bottle Conveyor Is Not Practical



Technical Specification:

✓ Input power: 230 V, AC, 50 Hz✓ Output power: 500 watts maximum.

☑ Can seal foil caps up to 8 to 10 bottle/minute.

☑ Cap size: 20 mm -100 mm

☑ Dimension: 400 mm x 340 mm x 690 mm (LXBXH)

☑ Weight: 23 Kg Net /Packed: 40 kg



Eltech Engineers

A-108, Diamond Ind Estate, Ketkipada Road, Nr.Toll Naka, Off W. E.Highway,

Dahisar (East), Mumbai-400068. Tel: 022-2897 2424 / 2626

Email: rajesh@eltech.in / eltech.rajesh@gmail.com

Website: www.eltech.in